

Цифровые вискозиметры серии LCH-NDJ

Технические характеристики

По вопросам продаж и поддержки обращайтесь:

Алматы (727)345-47-04
Ангарск (3955)60-70-56
Архангельск (8182)63-90-72
Астрахань (8512)99-46-04
Барнаул (3852)73-04-60
Белгород (4722)40-23-64
Благовещенск (4162)22-76-07
Брянск (4832)59-03-52
Владивосток (423)249-28-31
Владикавказ (8672)28-90-48
Владимир (4922)49-43-18
Волгоград (844)278-03-48
Вологда (8172)26-41-59
Воронеж (473)204-51-73
Екатеринбург (343)384-55-89

Иваново (4932)77-34-06
Ижевск (3412)26-03-58
Иркутск (395)279-98-46
Казань (843)206-01-48
Калининград (4012)72-03-81
Калуга (4842)92-23-67
Кемерово (3842)65-04-62
Киров (8332)68-02-04
Коломна (4966)23-41-49
Кострома (4942)77-07-48
Краснодар (861)203-40-90
Красноярск (391)204-63-61
Курск (4712)77-13-04
Курган (3522)50-90-47
Липецк (4742)52-20-81

Магнитогорск (3519)55-03-13
Москва (495)268-04-70
Мурманск (8152)59-64-93
Набережные Челны (8552)20-53-41
Нижний Новгород (831)429-08-12
Новокузнецк (3843)20-46-81
Ноябрьск (3496)41-32-12
Новосибирск (383)227-86-73
Омск (3812)21-46-40
Орел (4862)44-53-42
Оренбург (3532)37-68-04
Пенза (8412)22-31-16
Петрозаводск (8142)55-98-37
Псков (8112)59-10-37
Пермь (342)205-81-47

Ростов-на-Дону (863)308-18-15
Рязань (4912)46-61-64
Самара (846)206-03-16
Санкт-Петербург (812)309-46-40
Саратов (845)249-38-78
Севастополь (8692)22-31-93
Саранск (8342)22-96-24
Симферополь (3652)67-13-56
Смоленск (4812)29-41-54
Сочи (862)225-72-31
Ставрополь (8652)20-65-13
Сургут (3462)77-98-35
Сыктывкар (8212)25-95-17
Тамбов (4752)50-40-97
Тверь (4822)63-31-35

Тольятти (8482)63-91-07
Томск (3822)98-41-53
Тула (4872)33-79-87
Тюмень (3452)66-21-18
Ульяновск (8422)24-23-59
Улан-Удэ (3012)59-97-51
Уфа (347)229-48-12
Хабаровск (4212)92-98-04
Чебоксары (8352)28-53-07
Челябинск (351)202-03-61
Череповец (8202)49-02-64
Чита (3022)38-34-83
Якутск (4112)23-90-97
Ярославль (4852)69-52-93

Россия +7(495)268-04-70

Казахстан +(727)345-47-04

Беларусь +(375)257-127-884

Узбекистан +998(71)205-18-59

Киргизия +996(312)96-26-47


эл.почта: apv@nt-rt.ru || сайт: <https://lchoi.nt-rt.ru/>



LCH-NDJ Digital Temperature Rotational Viscometer


Features:

- LCD blue backlight screen
- Microcomputer control technology
- Accuracy Measuring



MODEL	LCH-NDJ-5S	LCH-NDJ-8S	LCH-NDJ-5S PRO	LCH-NDJ-8S PRO
Power supply	AC220V±10,50Hz±10%			
Power (W)	5			
Display	LCD			
Measurement range (mPa.s)	1-1×10^5	1-2×10^6	1-1×10^5	1-2×10^6
Spindle specification	No.1-4 Spindle (optional 0#Spindle)			
Spindle speed (rpm)	6/12/30/60	0.3/0.6/1.5/3/6 /12/30/60	6/12/30/60	0.3/0.6/1.5/3/6 /12/30/60
Measurement accuracy	±2%(Newtonian liquid)			
Repeatability error	±1%(Newtonian liquid)			
Temperature accuracy	/		±0.2℃	
RS232 interface	Optional			
Timing function	√			
Net weight (Kg)	4			
Product size (mm)	276*270*500			

PRODUCT STRUCTURE




FREE LIFTING SYSTEM

Easy and convenient up and down movement, stable support to resist slipping, meeting various container depths.



Equipped with multiple specifications of rotors and using different samples.



Optional 0#Spindle

Suitable for measuring low viscosity liquids with viscosity below $100\text{ mPa}\cdot\text{s}$, with a minimum measurement of $0.1\text{ mPa}\cdot\text{s}$ for low viscosity samples, requiring only 25ml of sample capacity.



PRODUCT DETAILS

01

LEVEL BUBBLE



02

HORIZONTAL
ADJUSTMENT KNOB

